

TECHSPEC® 12mm C VIS-NIR Series Fixed Focal Length Lens



12mm C VIS-NIR Series Fixed Focal Length Lens

Stock **#27-554** 20+ In Stock

-

1

+

€441⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€441,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

C VIS-NIR Series	Series:
Fixed Focal Length Lens	Type:

Imaging Lens Type:
Compact Lens Coated for Visible to Near Infrared

Physical & Mechanical Properties

Iris Option:

Variable	
27.90	Length (mm):
32.0	Maximum Diameter (mm):
32	Outer Diameter (mm):
54	Weight (g):
0.5	Maximum Rear Protrusion (mm):

Optical Properties

41.2°	Horizontal Field of View @ Max Sensor Format:
	Field of View at Max Sensor Format: Horizontal: 41.4° Vertical: 31.4° Diagonal: 50.8°
41.4°	Horizontal Field of View, 2/3" Sensor:
34.2°	Horizontal Field of View, 1/1.8" Sensor:
30.5°	Horizontal Field of View, 1/2" Sensor:
27.7°	Horizontal Field of View, 1/2.5" Sensor:
23.0°	Horizontal Field of View, 1/3" Sensor:
17.3°	Horizontal Field of View, 1/4" Sensor:
11.00	Maximum Image Circle (mm):
0.0285	Numerical Aperture NA, Object Side:
7 (7)	Number of Elements (Groups):
12.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/1.8 - f/16	Aperture (f/#):
425 - 1000nm BBAR	Coating:
425 - 1000nm BBAR	Coating Specification:
11.01	Entrance Pupil Position (mm):
17.20	Object Space Principal Plane (mm):
2.05	Image Space Principal Plane (mm):
-2.2	Maximum Distortion (%):
-10.84	Exit Pupil Position (mm):
VIS-NIR	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

M25.5 x0.50 (Female)	Filter Thread:
C-Mount	Mount:

Environmental & Durability Factors

-20 to +60	Storage Temperature (°C):
For questions regarding operating	

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C) Broadband Lens for 425-1000nm Wavelength Range
- 3.5mm to 50mm Focal Length

TECHSPEC® C Series Fixed Focal Length VIS-NIR Lenses are designed for use in machine vision applications that require NIR or VIS-NIR performance, with the working distance and resolution requirements of factory automation and inspection in mind. Featuring large maximum apertures and a Broadband Anti-Reflection (BBAR) coating designed out to 1000nm, these high performance lenses can be used in even the most restrictive lighting conditions. TECHSPEC® C Series Fixed Focal Length VIS-NIR Lenses are manufactured to a high tolerance, resulting in greater levels of imaging performance and low lens-to-lens variation, assuring simple installing into multiple systems. By combining high optical performance, industrial features, and small package size, the C Series Fixed Focal Length VIS-NIR Lenses represent a new standard in factory automation optics.

Also available with a [VIS Broadband Anti-Reflection \(BBAR\)](#) or [SWIR](#) Coatings

Note: For IR imaging alone, [UV-VIS Cut Filters](#) are available and thread directly onto the front filter threads of the 4.5mm, 16mm, 25mm, 35mm and 50mm FL lenses.

Technical Information

Focal Length	A	B	C	D
3.5mm	50.0mm	39.3mm	32.0mm	2.72mm
4.5mm	40.0mm	37.5mm	32.0mm	2.78mm
6.0mm	36.0mm	48.9mm	35.8mm	1.4mm
8.5mm	32.0mm	34.5mm	32.0mm	0.0mm
12mm	32.0mm	27.9mm	32.0mm	0.5mm
16mm	33.0mm	40.5mm	33.0mm	1.0mm
25mm	31.0mm	30.5mm	31.0mm	1.3mm
35mm	33.0mm	41.0mm	33.0mm	0.0mm
50mm	35.8mm	53.7mm	35.8mm	2.85mm
100mm	52.0mm	93.5mm	41.0mm	7.0mm

Max. Rear Protrusion (D)

Overall Max. Length (B)

Max. Outer Diameter Thread (A)

Filter Diameter Thread

Mounting Diameter (C)

Focus Adjustment

Focus Locking Screw

Iris Locking Screw

Iris Adjustment

C-Mount