

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.7 mm Diameter x 200mm FL, 370-550nm Coated, Ultrarast Thin PCX Lens



Stock #11-676 3-4 DAYS

[Other Coating Options](#)

1

€95,00

ADD TO CART

Qty 1-5

€95,00

Qty 6+

€84,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.10

Effective Focal Length EFL (mm):
200.23 @587.6nm

Back Focal Length BFL (mm):

199.20
Coating: BBAR (370-550nm)
Coating Specification: R _{abs} <0.55% @ 370 - 550nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.50 ±0.10
Edge Thickness ET (mm): 1.28
Radius R₁ (mm): 91.80
Clear Aperture CA (mm): 11.43
f/#: 15.75
Numerical Aperture NA: 0.032
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 370 - 550
Angle of Incidence (°): 0
Damage Threshold, By Design: ☐ 7.5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View