

TECHSPEC®

12.7mm Thick Inner Single Optic Mount



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock **#38-757** **1 In Stock**

-

1

+

€35⁰²

ADD TO CART

Volume Pricing	
Qty 1-4	€35,02 each
Qty 5+	€33,27 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Fixed

Type:

Function:

Optic Mount (Fixed)	
Physical & Mechanical Properties	
Construction:	Matte Black Anodized Aluminum (6061-T6)
Total Length (mm):	14.0
Clear Aperture CA (mm):	11.2
Max. Thickness of Compatible Optics (mm):	9.0
Min. Thickness of Compatible Optics (mm):	1.0
Edge Thickness of Compatible Optics (mm):	9.0
Threading & Mounting	
Diameter of Compatible Optics (mm):	12.7
Thread Type:	M29 x0.75
Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View

PRODUCT DETAILS

- Mounts for a Variety of Optical Component Diameters and Thicknesses
 - M29 Outer Diameter Threads Allow Easy Positioning Within [Outer Tubes](#)
 - One Retainer Ring and One Delrin Ring are Included
 - Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.
- TECHSPEC® Multi-Element Inner Single Optic Mounts are designed to mount a variety of optical components. The mounts support optical diameters from 5mm to 25.4mm, and edge thicknesses of 4mm to 17mm. With M29 x 0.75 outer diameter threads, these mounts can be easily positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Single Optic Mounts include one Delrin ring to ensure secure clamping force between the retainer ring and optic without damaging the optic.
- Note:** Our specially designed ME Spanner Wrench ([#13-567](#)) is highly recommended to move Inner Single Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench ([#11-046](#)) is also available.