

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12mm Dia. X 24mm FL, NIR I, Inked, Double-Convex Lens



Stock #33-392-INK [CONTACT US](#)

[Other Coating Options](#)

- 1 +

€52,50

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €52,50                        |
| Qty 10+                       |
| €47,25                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.00 ±0.025

Back Focal Length BFL (mm):

|                                                                                                    |
|----------------------------------------------------------------------------------------------------|
| 22.65                                                                                              |
| <b>Effective Focal Length EFL (mm):</b><br>24.00                                                   |
| <b>Coating:</b><br>NIR I (600-1050nm)                                                              |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm                             |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                                |
| <b>Surface Quality:</b><br>40-20                                                                   |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                              |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                        |
| <b>Centering (arcmin):</b><br><1                                                                   |
| <b>Bevel:</b><br>Protective bevel as needed                                                        |
| <b>Center Thickness CT (mm):</b><br>4.00                                                           |
| <b>Center Thickness Tolerance (mm):</b><br>±0.05                                                   |
| <b>Edge Thickness ET (mm):</b><br>2.48                                                             |
| <b>Radius R<sub>1</sub>=R<sub>2</sub> (mm):</b><br>24.108                                          |
| <b>Clear Aperture CA (mm):</b><br>11.00                                                            |
| <b>f/#:</b><br>2.00                                                                                |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                        |
| <b>Numerical Aperture NA:</b><br>0.25                                                              |
| <b>Type:</b><br>Double-Convex Lens                                                                 |
| <b>Wavelength Range (nm):</b><br>600 - 1050                                                        |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>7 J/cm <sup>2</sup> @ 1064nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |