

12mm Dia. x 6mm FL Protected Aluminum, Concave Mirror



Stock #43-462 **20+ In Stock**

⊖ 1 ⊕ €49⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-49	€49,00 each
Qty 50-99	€42,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

±0.5 **Thickness Tolerance (mm):**

12.00 ±0.50 **Diameter (mm):**

90 Clear Aperture (%):

3.0 Edge Thickness ET (mm):

Optical Properties

Metal Coating Type:

Protected Aluminum (400-2000nm) Coating:

400 - 2000 Wavelength Range (nm):

6.00 Effective Focal Length EFL (mm):

N-BK7 Substrate:

f/0.5 Aperture (f#):

Coating Specification:
R_{avg} > 85% @ 400 - 700nm
R_{avg} > 90% @ 400 - 2000nm

±2 Focal Length Tolerance (%):

12.00 Radius R₁ (mm):

80-50 Surface Quality:

12.00 Radius of Curvature (mm):

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

Technical Information

