

TECHSPEC® 135mm EFL MgF₂ Coated, UV-NIR Corrected Triplet



Stock **#64-839** 3-4 DAYS

- 1 + **€2.575,00**

ADD TO CART

Qty 1-5
€2.575,00
Qty 6+
€2.189,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
135.00

Focal Length Tolerance (%):
±1.5 @ 248nm

Back Focal Length BFL (mm):
129.31

Back Focal Length BFL from Housing (mm):

126.9
Clear Aperture CA (mm): 22.5
Substrate: ☐ CaF ₂ / Fused Silica / CaF ₂
Surface Quality: 60-40
f#: 6.00
Numerical Aperture NA: 0.08
Coating: MgF ₂ (193-1000nm)
Coating Specification: MgF ₂ @ 600nm
Effective Focal Length EFL @ 248nm (mm): 135.00
Housing Diameter (mm): 30.00 ±0.05
Housing Length (mm): 20.50 ±0.05
Type: Achromatic Triplet Lens
Wavelength Range (nm): 193 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 205: Compliant
Certificate of Conformance: View