

TECHSPEC[®] 12mm LT Series Fixed Focal Length Lens



12mm FL Front, #14-361



Stock **#14-361** CLEARANCE **2 In Stock**

-

1

+

 €1.435⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.435,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

LT Series	Series:
Diameter includes liquid lens	Note:
	Type:

Fixed Focal Length Lens	
Integrated Liquid Lens Model: Optutune EL-16-40-TC	
Imaging Lens Type: Integrated Liquid Lens to Adjust Focus Electronically	
Special Type of Lens: Liquid Lens Focusable	

Physical & Mechanical Properties

Iris Option: Fixed	
Length (mm): 74.30	
Maximum Diameter (mm): 82	
Outer Diameter (mm): 82	
Weight (g): 245.5	
Maximum Rear Protrusion (mm): 0	

Optical Properties

Horizontal Field of View @ Max Sensor Format: 432.6mm - 60.0°	
Field of View at Max Sensor Format: Horizontal: 434.3mm - 59.2° Vertical: 321mm - 45.7° Diagonal: 552.2mm - 71.5°	
Horizontal Field of View, 1.1" Sensor: 432.6mm - 60.0°	
Horizontal Field of View, 1" Sensor: 387.6mm - 54.7°	
Horizontal Field of View, 2/3" Sensor: 262.3mm - 38.8°	
Horizontal Field of View, 1/1.8" Sensor: 213.6mm - 32.0°	
Horizontal Field of View, 1/2" Sensor: 189.4mm - 28.5°	
Horizontal Field of View, 1/2.5" Sensor: 171.4mm - 25.9°	
Horizontal Field of View, 1/3" Sensor: 141.5mm - 21.5°	
Horizontal Field of View, 1/4" Sensor: 105.9mm - 16.2°	
Maximum Image Circle (mm): 17.60	
Numerical Aperture NA, Object Side: 0.006	
Number of Elements (Groups): 10 (9)	
Focal Length FL (mm): 12.00	
Working Distance (mm): 350 - ∞	
Aperture (f/#): f/2.8	
Coating: λ/4 MgF ₂	
Coating Specification: λ/4 MgF ₂	
Entrance Pupil Position (mm): 31.2	
Object Space Principal Plane (mm): 39.92	
Image Space Principal Plane (mm): 2.45	
Maximum Distortion (%): -4.23	
Exit Pupil Position (mm): -26.58	
Lens Wavelength Range: VIS	

Sensor

Maximum Sensor Format:	
1.1"	
Pixel Size (µm):	
2.74	
Threading & Mounting	
Filter Thread:	
M62 x0.75 (Male)	
Filter Thread Adapter:	
#34-236 (Required)	
Front Thread:	
M48 x0.5 (Male)	
Mount:	
C-Mount	
Environmental & Durability Factors	
Storage Temperature (°C):	
-20 to +60	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details


- 1.1" Sensor, C-Mount Lens, up to 12 MegaPixels, 3.45µm Pixel Size Sensor
- Integrated Liquid Lens Allows for Dynamic Autofocus
- Liquid Tunable (LT) Lens Maximizes the Liquid Lens Capabilities for Resolution, Range and Focus Speed
- 12 to 25mm Focal Length

TECHSPEC® LT Series Fixed Focal Length Lenses feature a high-resolution f/2.8 optical design with an integrated Optotune liquid lens for fast electronic focus. The increased light throughput f/2.8 aperture is ideal for high-speed machine vision applications. When combined with an appropriate camera and software, the focus tunable liquid lens provides the active focus control needed to achieve an autofocus solution. These C-Mount lenses are optimized for 1.1" sensors and have front filter threading to integrate imaging filters to meet application requirements. TECHSPEC® LT Series Fixed Focal Length Lenses are ideal for machine vision and factory automation applications where focusing at multiple distances is required, such as quality inspection systems, rapid automation, and package sorting. The TECHSPEC® LT Series Fixed Focal Length Lenses won the [Gold-Level 2021 Vision Systems Design Innovators Award](#) and [third place 2021 reader's choice inspect Award](#).


inspect award 2021 winner

Note: Hirose cables (2 length options) and Lens Driver are required for operation and sold separately.


Technical Information




#14-361, 12mm LT Series Fixed Focal Length Lens, Distortion Plot




#14-361, 12mm LT Series Fixed Focal Length Lens, Relative Illumination Plot




#14-361, 12mm LT Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#14-361, 12mm LT Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f2.8




#14-361, 12mm LT Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f2.8



#14-361, 12mm LT Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 1000mm Working Distance, f2.8



#14-361, 12mm LT Series Fixed Focal Length Lens, Depth of Field Plot, 1000mm Working Distance, f2.8



Compatible Cameras