

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

1550nm Flat Top Beam Shaper | πSnaper 6_6_1550

See More by [AdiOptica](#)



Flat Top Beam Shaper

Stock **#37-700** [CONTACT US](#)



1



€6.159,00

ADD TO CART

Qty 1-4

€6.159,00

Qty 5+

€5.541,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
1550

Diameter (mm):
39.00

Entrance Beam Diameter, 1/e² (mm):
6.4-6.5

Model Number: πShaper 6_6_1550
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <270
Wavelength Range (nm): 1500 - 1600
Style: Flat Top
Damage Threshold, By Design: ☐ 20 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 6.2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant