

**TECHSPEC® 15mm Dia. 2mm Thick MgF<sub>2</sub> Coated, 1λ Fused Silica Window**



Stock #11-921 3-4 DAYS

⊖ 1 ⊕ **€76,00**

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €76,00  |

|        |
|--------|
| Qty 6+ |
| €60,75 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v<sub>d</sub>):  
67.8

Bevel:  
Protective as needed

Clear Aperture (%):  
90

|                                                                                                                                        |
|----------------------------------------------------------------------------------------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>13.50                                                                                                |
| <b>Diameter (mm):</b><br>15.00 +0.00/-0.20                                                                                             |
| <b>Thickness (mm):</b><br>2.00 ±0.38                                                                                                   |
| <b>Coating:</b><br>MgF <sub>2</sub> (400-700nm)                                                                                        |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤1.75% @400 - 700nm                                                                  |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) |
| <b>Density (g/cm³):</b><br>2.20                                                                                                        |
| <b>Edges:</b><br>Fine Ground                                                                                                           |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.458                                                                                     |
| <b>Knoop Hardness (kg/mm²):</b><br>522                                                                                                 |
| <b>Parallelism (arcmin):</b><br><5                                                                                                     |
| <b>Poisson's Ratio:</b><br>0.16                                                                                                        |
| <b>Substrate:</b><br><a href="#">Fused Silica</a> (Corning 7980)                                                                       |
| <b>Surface Flatness (P-V):</b><br>1λ                                                                                                   |
| <b>Surface Quality:</b><br>60-40                                                                                                       |
| <b>Type:</b><br>Protective Window                                                                                                      |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                                                             |
| <b>Young's Modulus (GPa):</b><br>73                                                                                                    |
| <b>Damage Threshold, By Design:</b> ☐<br>10 J/cm² @532nm, 10ns                                                                         |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |