

[See all 8 Products in Family](#)

## 152mm Dia x 30mm FL Alum. Coated, Parabolic Reflector



Stock #90-965 [CONTACT US](#)

- 1 + €770.<sup>00</sup>

[ADD TO CART](#)

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €770,00 each                  |
| Qty 11-25      | €682,00 each                  |
| Qty 26-49      | €644,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

! Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Parabolic Mirror **Type:**

### Physical & Mechanical Properties

152.00 +0.0/-0.5 **Diameter (mm):**

35.0 **Center Hole Diameter (mm):**

47.0 Height (mm):

## Optical Properties

Metal Coating Type:

Protected Aluminum (400-700nm) Coating:

400 - 700 Wavelength Range (nm):

BOROFLOAT® Substrate:

0.197 Aperture (f#):

$R_{avg} > 85\%$  @ 400 - 700nm Coating Specification:

30.00 Focal Length FL (mm):

## Regulatory Compliance

[View](#) Certificate of Conformance:


## Product Details

- Precision Polished Substrate
- Protected Aluminum and Cold Mirror Coating Options
- Ideal for Highly Divergent Light Sources
- [Precision Ellipsoidal Reflectors](#) Also Available

Precision Parabolic Reflectors are ideal for collimating a light source placed at the focal point of the mirror. The parabolic profile eliminates spherical aberration, allowing the light source to maintain its wavefront characteristics. These Precision Parabolic Reflectors feature very low f#s, making them ideal for highly divergent light sources. The protected aluminum coating features broadband high reflection through the visible and IR spectra. The cold mirror coating reflects visible light while transmitting NIR, making it ideal for cold condensing applications.

Precision Parabolic Reflectors are precision polished, yielding exact aspheric profiles. These mirrors offer improved thermal stability and superior focusing efficiency versus commercially available press-molded reflectors. Typical applications include use as steppers for PCB, LCD, or PDP production, solar simulators, fiber optic illuminators, and projectors.

## Technical Information



| Diameter | Focal Length f | Center Hole Diameter d | Height H | Stock No.               |
|----------|----------------|------------------------|----------|-------------------------|
| 100mm    | 12.5mm         | —                      | 45mm     | <a href="#">#90-964</a> |
|          |                |                        |          | <a href="#">#90-967</a> |
|          | 19mm           | 30mm                   | 32mm     | <a href="#">#68-791</a> |
| 152mm    | 17mm           | 30mm                   | 79mm     | <a href="#">#68-792</a> |
|          | 30mm           | 35mm                   | 47mm     | <a href="#">#90-965</a> |
| 220mm    | 100mm          | —                      | 33mm     | <a href="#">#68-793</a> |
| 300mm    | 42mm           | —                      | 130mm    | <a href="#">#90-966</a> |

