

[See all 24 Products in Family](#)

# 1550nm HP Flat Top Beam Shaper | πShaper 12\_12\_1550\_HP

See More by [AdlOptica](#)



Stock #25-841 **1 In Stock**

⊖ 1 ⊕ €9.110<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€9.110,00 each
Qty 5+	€8.110,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

πShaper 12\_12\_1550\_HP **Model Number:**

Beam Shaper **Type:**

Flat Top **Style:**

### Physical & Mechanical Properties

358.00 Length (mm):

<300 Weight (g):

49.00 Diameter (mm):

### Optical Properties

12 Entrance Beam Diameter,  $1/e^2$  (mm):

1550 Design Wavelength DWL (nm):

1500 - 1600 Wavelength Range (nm):

3000 mJ/cm<sup>2</sup> @ 5ns (typical) Damage Threshold, By Design:

12.2 Output Diameter, FWHM (mm):

3000 mJ/cm<sup>2</sup> @ 5ns (typical) Damage Threshold, Pulsed:

### Threading & Mounting

Input: M27 x 1  
Output: M33 x 2 Mounting Threads:

### Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:


Compliant Reach 250:

## Product Details

- Convert Gaussian Beam Profile to Flat Top Profile
- Near 100% Efficiency
- No Internal Focusing Enables High Power Laser Input
- [AdlOptica Focal- \$\pi\$ Shaper Q Flat Top Beam Shapers](#) Also Available

AdlOptica  $\pi$ Shaper ( $\pi$ Shaper) Flat Top Beam Shapers are refractive field mapping optical systems that convert collimated Gaussian input beams into collimated flat top beams with a uniform intensity distribution and flat phase front. Due to the field mapping optical design, the even intensity distribution of the converted beam is stable over great distances making it ideally suitable for holography, microscopy, and system integration. With no internal focusing, they are also the perfect solution in applications such as material micromachining, welding, and engraving that require high power lasers. These AdlOptica  $\pi$ Shaper Flat Top Beam Shapers are offered in common YAG, fiber laser, and CO<sub>2</sub> laser sources, operating over a defined wavelength range for laser tuning. Achromatic versions are designed to be used with multiple laser sources.

**Note:** Focusing a flat-top beam after a  $\pi$ Shaper results in loss of the flat top profile. [AdlOptica Focal- \$\pi\$ Shaper Q Flat Top Beam Shapers](#) are available for applications that require a focused flat top spot.



## Technical Information

Example of beam shaping for TEM<sub>00</sub> Laser

