

[See all 20 Products in Family](#)

## 15° Diffusing Angle 25mm Dia., Fused Silica Holographic Diffuser



UV Fused Silica Holographic Diffusers

Stock **#48-507** [CONTACT US](#)

⊖ 1 ⊕ €499<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€499,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Holographic Diffuser **Type:**

### Physical & Mechanical Properties

21.6 ±0.1 **Clear Aperture CA (mm):**

25.00 ±0.1 **Diameter (mm):**

**Construction:**

Mounted

## Optical Properties

±1.5 **Angle Tolerance (°):**

15 (FWHM) **Diffusing Angle (°):**

**Substrate:**   
[Fused Silica](#) (Coming 7980)

Typical: 90 **Transmission (%):**

400 - 700 **Wavelength Range (nm):**

## Threading & Mounting

5.00 +0.00/-0.35 **Mount Thickness (mm):**

## Environmental & Durability Factors

-40 to +170 **Operating Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

## Product Details




- Diffusing Angles Ranging from 0.5 - 50°
- Fused Silica Substrate Ideal for High Temperatures
- Homogenous Light Distribution
- [Standard Holographic Diffusers](#) Also Available

UV Fused Silica Holographic Diffusers are used to control the diffuse area of illumination and increase transmission efficiency to greater than 90% from filament lamps, LEDs, arc lamps, and other sources. These UV Fused Silica Holographic Diffusers use a fused silica substrate enabling their use at higher operating temperature than [polycarbonate holographic diffusers](#) and offer controlled, homogenous light distribution. It is important to note that diffusing angles are given for a collimated input beam and angular divergence will vary for different incidence angles.

Unlike many holographic elements, these specific fused silica components transmit light in the UV, visible, and near-infrared. Zero order, or a specular component, of transmitted light is less than 1% for visible wavelengths. Diffusers with wider diffusing angles (10 degree FWHM or wider) can also be used in an extended range of 200-1500nm, but those with lower diffusing angles are only recommended for use between 400-700nm.

**Note:** Matte surface should face the light source. To clean holographic diffusers, dampen a lint free cloth wipe with methanol and gently wipe the entire diffuser surface in a gentle, circular pattern. Immediately and carefully blow off the clean diffuser area with dry compressed air. Caution: cleaning may cause a change in the optical performance of the diffuser.

## Technical Information



## Compatible Mounts

---