

[See all 280 Products in Family](#)

TECHSPEC[®] 15mm Dia. x 50mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-337-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

€125^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€125,00 each
Qty 6-25	€100,00 each
Qty 26-49	€94,50 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens

Type:

Physical & Mechanical Properties

15.00 ±0.025	Diameter (mm):
14.00	Clear Aperture CA (mm):
<1	Centering (arcmin):
6.50 ±0.20	Center Thickness CT (mm):
5.00 ±0.10	Center Thickness CT 1 (mm):
1.50 ±0.10	Center Thickness CT 2 (mm):
5.12	Edge Thickness ET (mm):
Protective as needed	Bevel:

Optical Properties	
50.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
46.17	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
26.81	Radius R ₁ (mm):
-23.82	Radius R ₂ (mm):
-90.79	Radius R ₃ (mm):
N-BK7 / N-SF5	Substrate: ☐
40-20	Surface Quality:
3.33	f/#:
0.15	Numerical Aperture NA:
VIS-NIR (400-1000nm)	Coating:
R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
400 - 1000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

Product Details

- Designed for 0° Angle of Incidence
- Less Than 0.25% Reflectance Per Surface @ 880nm
- **MgF₂** and **VIS 0°** Coated Achromats Also Available

TECHSPEC® VIS-NIR Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. TECHSPEC® VIS-NIR Coated Achromatic Lenses have visible/near-infrared broadband anti-reflection coating, which is specially optimized to yield maximum transmission (>99%) in the near-infrared. The achromatic lenses reduce reflection to less than 0.25 percent per surface at 880nm. **Magnesium Fluoride** coated and **VIS 0°** coated achromats are also available.

Technical Information



Coating Curves

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts