

TECHSPEC<sup>®</sup> 15mm  $\lambda/20$ , 1064nm V-Coat, Nd:YAG Right Angle Prism



TECHSPEC Nd:YAG Laser Line  $\lambda/20$  UV Fused Silica Right Angle Prisms

Stock **#37-637** [CONTACT US](#)

-

1

+

€377<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €377,00 each                  |
| Qty 6-25       | €302,00 each                  |
| Qty 26-49      | €283,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                          |                             |
|----------------------------------|-----------------------------|
| Right Angle Prism                | Type:                       |
| Physical & Mechanical Properties |                             |
| +0.00/-0.10                      | Dimensional Tolerance (mm): |
|                                  | Bevel:                      |


|                                  |                                |
|----------------------------------|--------------------------------|
| Protective as needed             |                                |
| 90                               | Clear Aperture (%):            |
| 21.20                            | Length of Hypotenuse (mm):     |
| 15.00                            | Length of Legs (mm):           |
| Optical Properties               |                                |
| ±15                              | Angle Tolerance (arcsec):      |
| Laser V-Coat (1064nm)            | Coating:                       |
| 1064                             | Design Wavelength DWL (nm):    |
| Fused Silica (Corning 7980)      | Substrate: □                   |
| 20-10                            | Surface Quality:               |
| ±1                               | Pyramid Tolerance (arcmin):    |
| Left-Handed                      | Image Orientation:             |
| R <sub>abs</sub> <0.25% @ 1064nm | Coating Specification:         |
| λ/20                             | Surface Flatness (P-V):        |
| 15 J/cm², 20ns, 20 Hz            | Damage Threshold, By Design: □ |
| Regulatory Compliance            |                                |
| Compliant                        | RoHS 2015:                     |
| Compliant                        | Reach 209:                     |
| View                             | Certificate of Conformance:    |

## Product Details

- λ/20 Surface Flatness
- <0.25% Reflection for Nd:YAG Applications
- 5 - 25mm Sizes Available

TECHSPEC® Nd:YAG Laser Line λ/20 Fused Silica Right Angle Prisms offer a combination of precision surface flatness and guaranteed laser damage threshold AR coatings. These prisms are ideal for beam steering with minimal wavefront distortion due to λ/20 surface flatness on all faces. A±15 arcsecond angular tolerance ensures consistent alignment for volume integration. TECHSPEC® Nd:YAG Laser Line λ/20 Fused Silica Right Angle Prisms are designed for transmission through the anti-reflection coated legs of the prism, resulting in a 90° turn in beam direction. A vertically integrated manufacturing process ensures these prisms are easily scaled for custom requests.

## Technical Information






Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).