

TECHSPEC® 16mm, f/1.8 UCi Series Fixed Focal Length Lens



16mm UCi Series Fixed Focal Length Lens



Stock #33-883 **20+ In Stock**

− 1 + €235⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€235,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Series:

UCi Series

Fixed Focal Length Lens **Type:**

No **IR Cut Filter:**

High Performance Lens with Compact Form Factor and Fixed Aperture **Imaging Lens Type:**

Physical & Mechanical Properties

Fixed **Iris Option:**

26.70 **Length (mm):**

18 **Maximum Diameter (mm):**

25 **Outer Diameter (mm):**

13 **Weight (g):**

0 **Maximum Rear Protrusion (mm):**

25.5 **Maximum Length (mm):**

Optical Properties

98.5mm - 25.3° **Horizontal Field of View @ Max Sensor Format:**

Horizontal: 93.6mm - 25.3°
Vertical: 70.2mm - 19.1°
Diagonal: 117mm - 31.3° **Field of View at Max Sensor Format:**

93.6mm - 25.3° **Horizontal Field of View, 1/1.8" Sensor:**

83.2mm - 22.5° **Horizontal Field of View, 1/2" Sensor:**

75.4mm - 20.5° **Horizontal Field of View, 1/2.5" Sensor:**

62.4mm - 17.0° **Horizontal Field of View, 1/3" Sensor:**

46.8mm - 12.8° **Horizontal Field of View, 1/4" Sensor:**

9.00 **Maximum Image Circle (mm):**

0.0207 **Numerical Aperture NA, Object Side:**

7 (5) **Number of Elements (Groups):**

16.00 **Focal Length FL (mm):**

200 - ∞ **Working Distance (mm):**

f/1.8 **Aperture (f/#):**

N4 MgF₂ **Coating:**

N4 MgF₂ **Coating Specification:**

10.68 **Entrance Pupil Position (mm):**

20.18 **Object Space Principal Plane (mm):**

-6.67 **Image Space Principal Plane (mm):**

-0.53 **Maximum Distortion (%):**

-29.94 **Exit Pupil Position (mm):**

VS **Lens Wavelength Range:**

Sensor

1/2.5" **Optimized Sensor Format:**

1/1.8" **Maximum Sensor Format:**

1.85

Pixel Size (µm):

Threading & Mounting

Filter Thread:
M18 x 0.50 (Male)

Mount:
S-Mount (M12 x 0.5)

Environmental & Durability Factors

Storage Temperature (°C):
-20 to +60

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

Certificate of Conformance:
[View](#)

PRODUCT DETAILS

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels ≤2.2µm and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

Note: For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:


UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.


UCr Series: All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.


TECHNICAL INFORMATION




#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Distortion Plot




#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Relative Illumination Plot




#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 300mm Working Distance, f1.8



#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Depth of Field Plot, 300mm Working Distance, f1.8



#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f1.8



#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f1.8

COMPATIBLE CAMERAS