

16mm FL SWIR Series Fixed Focal Length Lens



Stock #83-817 **2 In Stock**

- 1 + €2.286⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€2.286,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
1" SWIR Series Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

Length (mm):
52.90

42.0	Maximum Diameter (mm):
42	Outer Diameter (mm):
150	Weight (g):

Optical Properties

235	Field of View @ Min Working Distance (mm):
44.3°	Horizontal Field of View, 1" Sensor:
16.00	Maximum Image Circle (mm):
16.00	Focal Length FL (mm):
300 - ∞	Working Distance (mm):
f/1.4 - f/16	Aperture (f/#):
<-1.0	Distortion (%):
-1	Maximum Distortion (%):
SWIR	Lens Wavelength Range:

Sensor

1"	Maximum Sensor Format:
4.50	Pixel Size (µm):

Threading & Mounting

M35.5 x 0.50	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- 1", C-Mount Lens
- Spectral Range of 800 - 2000nm for InGaAs SWIR Sensors
- 8mm to 50mm Focal Lengths

Short Wave Fixed Focal Length Lenses are the best choice for use with SWIR cameras. The SWIR spectrum is an ideal choice for a variety of applications, including solar cell inspection, security, and biomedical imaging. When utilized in conjunction with a SWIR camera, these lenses will permit imaging through silicon, imaging outdoors without additional illumination, detecting bruising on fruit, and a host of additional infrared applications.

Technical Information



