

15mm Diameter x 12mm FL, Aspheric Condenser Lens



Stock **#46-660** 20+ In Stock

☐ Other Coating Options

-

1

+

€53^{.50}

ADD TO CART

Volume Pricing	
Qty 1-10	€53,50 each
Qty 11-49	€48,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads	
General	
Condenser Lens	Type:
Physical & Mechanical Properties	
15.00 +0.1/-0.3	Diameter (mm):
≤30	Centering (arcmin):

14	Clear Aperture CA (mm):
2.0	Edge Thickness ET (mm):
7.50 ±0.2	Center Thickness CT (mm):
Protective as needed	Bevel:
15.0	Diameter of Asphere (mm):
Plano	Shape of Back Surface:

Optical Properties	
12.00	Effective Focal Length EFL (mm):
0.63	Numerical Aperture NA:
8.2	Back Focal Length BFL (mm):
B270	Substrate: ☐
±7	Focal Length Tolerance (%):
Uncoated	Coating:
80-50 (typical)	Surface Quality:
0.8	f/#:
Plano	Radius R ₂ (mm):
350 - 2500	Wavelength Range (nm):
Infinite	Conjugate Distance:


Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information





Compatible Mounts

;