


TECHSPEC®

15mm UV Enhanced Aluminum Coated, N-BK7 Right Angle Prism



Stock #24-180 [CONTACT US](#)

-

1

+

€97,50

ADD TO CART

Qty 1-5
€97,50
Qty 6+
€78,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate:
[N-BK7](#)

Surface Quality:
60-40

Length of Legs (mm): 15.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R_{avg} >85% @ 250 - 700nm R_{avg} >89% @ 250 - 450nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 19.09 x 13.50
Length of Hypotenuse (mm): 21.20
Type: Right Angle Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 355nm, 10ns
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant