

[See all 12 Products in Family](#)

# 160mm, 900-1100nm JENar™ Silverline™ F-Theta Scanning Lens

See More by [Jenoptik](#)



Stock #17-021 **1 In Stock**

⊖ 1 ⊕ €6.885<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€6.885,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

601787 **Model Number:**

JENar Silverline F-Theta **Type:**

#17-694: One Included **Protective Window:**

Jenoptik **Manufacturer:**

## Physical & Mechanical Properties

119.8 +0/-0.2 **Maximum Diameter (mm):**

1080 **Weight (g):**

±7.1 **X/Y Mirror Angle (°):**

266.00 @ 900nm  
267.90 @ 1100nm **Flange Distance (mm):**

14 **Input Beam Diameter, 1/e<sup>2</sup> (mm):**

100 **Maximum Length (mm):**

## Optical Properties

160.00 **Focal Length FL (mm):**

**Substrate:**   
[Fused Silica](#) (Coming 7980)

±20 **Scan Angle (°):**

78 x 78 **Scan Field (mm):**

F-Theta Only: 5.20  
With Scanner: 5.40 **Telecentricity (°):**

182.00 @ 900nm  
183.90 @ 1100nm **Working Distance (mm):**

900 - 1100 **Wavelength Range (nm):**

110 **Scan Field Diameter (mm):**

19.0 @ 900nm  
23.0 @ 1100nm **Focus Size Diameter, 1/e<sup>2</sup> (µm):**

759 **GDD Specification (fs<sup>2</sup>):**

## Threading & Mounting

M85 x 1 **Mounting Threads:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Low-Absorption Fused Silica Substrates for High-Power Laser Applications
- Large Scan Fields Up to 328mm x 328mm
- High Damage Thresholds and Low Telecentricity Errors
- [Jenoptik JENar™ F-Theta Scanning Lenses](#) Also Available

Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses provide flat field at the image plane and feature low-absorption fused silica substrates, making them suitable for high-power laser applications. These F-Theta lenses offer high damage thresholds to handle beam powers of up to four kilowatts without active cooling and are available in various wavelengths ranging from 266nm to 1100nm. With large processing areas up to 328mm x 328mm, low telecentricity errors, and diffraction-limited image quality, these lenses allow for high spot consistency and increased throughput over the entire scanning range. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses were specially developed for applications requiring high-power and short-pulse Nd:YAG, Yb:doped, and fiber laser sources and are used in conjunction with [galvanometers](#) and [beam expanders](#).

Contact us if your application requires [Jenoptik JENar™ F-Theta Scanning Lenses](#) or Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses not shown on our website.