16.0mm FL, No IR-Cut Filter, f/2, Micro Video Lens

Stock **#64-108** **20+ In Stock**

Similar Products

- 1 + **€70**.00

ADD TO CART

Volume Pricing	
Qty 1-49	**€70,00** each
Qty 50+	**€56,00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
Long Working Distance Optimized Imaging Lenses

Note:
Standard

Type:
M12 Imaging Lens

IR Cut Filter:
No

Physical & Mechanical Properties

Iris Option:
Fixed

Length (mm):
14.40

Maximum Diameter (mm):
14.0

Outer Diameter (mm):
14

Optical Properties

Horizontal Field of View @ Max Sensor Format:
17

Maximum Image Circle (mm):
6.00

Resolution, On-Axis:
75 lp/mm @ 20% Contrast

Resolution, 0.7 Field:
65 lp/mm @ 20% Contrast

Resolution, Full Field:
60 lp/mm @ 20% Contrast

Focal Length FL (mm):
16.00

Working Distance (mm):
400 - ∞

Aperture (f/#):
f/2

Distortion (%):
-2.50 @ Full Field

Maximum Distortion (%):
-2.5

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
1/3"

Pixel Size (µm):
3.45

Threading & Mounting

Filter Thread:
M12 x 0.50

Mount:
S-Mount (M12 x 0.5)

Regulatory Compliance

RoHS 2015:
Exempt

Certificate of Conformance:
View

Reach 242:
Contains SVHC(s)

Product Details

- Up to 2/3", S-Mount Lens
- Wide Field of View Board Camera Lens
- 1.68mm to 50mm Focal Length

Long Working Distance Optimized Imaging Lenses are designed for use in micro sensor board cameras. These lenses provide excellent image quality in a small, versatile package. Optimized to cover 2/3" sensor formats, they are an ideal choice for wide angle and close focus applications. Long Working Distance Optimized Imaging Lenses have 1.68 to 50mm focal lengths. All lenses are threaded for M12 x 0.5. Some models with Back Focal Distances (dimension "C") less than 4mm may be incompatible with some color cameras due to the camera's Bayer filter. We recommend such lenses for use with monochrome cameras only. Lenses are designed for the 400nm to 700nm range.

Note: A line of **M12 Imaging Lens Accessories** is available for these products.

Technical Information



Infinite Conjugate M12 Imaging Lenses



C-Mount Adapter (#53-675)

Stock #		**Focal Length (mm)**	**Aperture (f/#)**	**A (mm)**	**B (mm)**	**C (mm)**	**D (mm)**	**E (mm)**
No-IR Cut Filter	**IR Cut Filter @650nm**							
#59-776	**#66-880**	1.68	2.5	15.0	13.2	3.3	2.8	15.1
#56-774	**#66-881****	1.74	2.8	21.0	19.61	3.33	3.2	N/A
#64-106	-	1.9	2.0	17.0	14.58	4.2	4.0	15.24
#55-569	**#66-883**	2.1	2.0	17.0	18.3	4.8	3.7	19.4
#57-681	**#66-884*****	2.5	2.5	17.0	19.1	4.4	3.7	20.3
#55-570	**#66-885**	2.9	2.0	15.0	17.4	5.2	5.8	17.8
#59-778	**#66-886**	3.0	2.0	14.0	15.3	5.3	3.9	N/A
#57-684	**#66-890**	6.05	1.8	15.0	15.6	8.0	6.0	N/A
#55-573	**#66-891**	6.37	2.4	14.8	13.12	5.3	3.3	N/A
#55-574	**#66-892**	8.0	2.5	15.0	13.5	5.8	3.0	N/A
#63-762	**#59-779**	10.1	2.8	15.0	13.4	6.1	3.2	N/A
#65-251	**#64-107**	10.4	2.8	14.0	8.93	6.4	4.0	N/A
#56-775	**#66-893**	12.0	2.0	14.0	12.1	6.2	4.0	N/A
#64-108	**#66-894**	16.0	2.0	14.0	14.4	8.0	4.5	N/A
#83-107	-	16.0	4.0	14.0	14.4	8.0	4.5	N/A
#56-776	**#66-895**	25.0	2.5	25.0	23.2	8.1	6.7	N/A
#59-780	**#66-896**	35.0	2.0	25.0	23.4	15.8*	6.0	N/A
#59-781	**#66-897**	50.0	2.5	27.0	52.8	4.1	8.0	N/A

***Note:** 35.0mm lens has a large flange focal length. Please make proper adjustments when mounting.
**#66-881, B(mm): 20.49
***#66-884, B(mm): 19.8, E(mm): 21

Stock #	Focal Length (mm)	Aperture (f/#)	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)
#88-587	3.0	2.0	15.0	15.35	5.2	4	16
#88-588	3.5	2.5	15.0	15.4	6.9	4	N/A
#11-323	3.7	1.6	19	24.04	5.46	6.5	24.16
#11-324	4.0	1.8	20	23.8	5.01	7	24.72
#88-589	4.0	2.0	15.0	16.1	5.9	3.8	N/A
#88-590	4.3	2.0	22.0	20.96	5.5	6	21.93
#11-325	4.6	1.6	19	24.18	5.44	7	24.32
#88-591	4.6	2.0	12.0	13.1	1.9	6	N/A
#88-592	5.6	2.0	17.0	22.21	5.3	5	22.38
#89-750	6.0	2.0	14.0	15.1	6.7	3.93	N/A
#11-326	7.0	1.6	19	25.24	5.47	7.2	24.2
#89-751	8.0	2.0	15.0	14.4	6.8	4.5	N/A
#89-752	12.0	2.0	15.0	14.3	5.7	4.5	N/A

;