

12mm Max. Aperture, Mounted AR Steel Leaves Iris Diaphragm



Standard Series

Stock **#23-258** [CONTACT US](#)

-

1

+

€91¹⁶

ADD TO CART

Volume Pricing	
Qty 1-4	€91,16 each
Qty 5-9	€80,34 each
Qty 10-25	€74,06 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Mounted

Type:

Physical & Mechanical Properties	
12.0	Maximum Aperture (mm):
39.0	Outer Diameter (mm):
Construction: Anodized Aluminum Alloy, Anti-Reflection (AR) Leaves	
19.8	Inner Diameter (mm):
3.00	Lever Diameter (mm):
10.00	Lever Length (mm):
11.00	Number of Leaves:
5.00	Thickness (mm):
Optical Properties	
1.0, Typical	Minimum Aperture (mm):
Threading & Mounting	
8-32	Mounting Threads:
4-40	Set Screw Thread:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- Corrosion and High Temperature Resistance Housing
 - Anti-Reflective (AR) Spring Steel or Burnished Spring Steel Leaf Options Available
 - Mounted Version Features both an English and Metric Tapped Hole for Easy Post Mounting
- High Performance Standard Series Iris Diaphragms utilize high-quality materials combined with the highest fabrication standards to guarantee optimum performance and reliability even under extreme environmental conditions. Different leaf and aperture diameter options allow these irises to be successfully integrated into a variety of applications, including imaging and high-temperature environments. Known pin/tab angular deviation allows upfront, accurate assessment of movement requirements. Mounted versions of these diaphragms feature both metric and English tapped holes for easy post mounting. These diaphragms are offered with maximum apertures of 5 – 75mm and that have outer diameters ranging from 10 to 100mm. High Performance Standard Series Iris Diaphragms are constructed of a corrosion-resistant, matte finish, black anodized aluminum alloy.
- For specific OEM application assistance, please contact our [Applications Engineering Department](#).
- Note:** [Iris Diaphragm Mounts](#) sold separately.

TECHNICAL INFORMATION

Outer Diameter A	Maximum Aperture B	Minimum Aperture C	Thickness D	Level Position E	Full Angular Range of Lever F	Stock No.
10mm	5mm	0.5mm	4mm	2.4mm	76°	#57-573
						#57-578
12mm	7mm	0.5mm	4mm	2.4mm	85°	#57-574
						#57-579
14.8mm	8mm	1mm	4.5mm	2.5mm	81°	#57-580
						#64-507
19.8mm	12mm	1mm	4mm	2.5mm	80°	#57-575
						#57-581
28mm	18mm	1mm	5mm	2.9mm	89°	#57-576
30mm	20mm	1.2mm	5.5mm	2.9mm	90°	#57-577
						#64-508
37mm	25mm	1.5mm	5.5mm	3mm	93°	#57-582
53mm	37mm	2.5mm	6mm	3.2mm	89°	#57-583
70mm	50mm	2.5mm	7mm	3.8mm	84°	#57-584

