


[All Products](#) / [Optics](#) / [Optical Mirrors](#)
/ [λ/4 Precision Spherical Mirrors](#)

[See all 120 Products in Family](#)

TECHSPEC® 1" Dia



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

1

€129⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9 €129,00 each

Qty 10-25 €108,00 each

Qty 26-49 €102,00 each

Need More? [Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:stp
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- Zemax:zar
- Zemax:zmx
- eDrawing:eprt
- Code V:seq
- EO Spec Sheet
- [Download All](#)

General

Type: Spherical Mirror

Physical & Mechanical Properties

Diameter (mm): 25.40 +0/-0.3

Back Surface: Ground

Diameter (inches): 1.0

Diameter Tolerance (inches): +0/-0.01

Edge Thickness ET (inches): 0.25

Edge Thickness ET (mm): 6.35

Edge Thickness Tolerance (%): +0.0/-15

Optical Properties

Coating Type: Metal

Coating: Protected Aluminum (400-2000nm)

Wavelength Range (nm): 400 - 2000

Effective Focal Length EFL (mm): 76.20

Substrate: **BOROFLOAT®**

Aperture (f/#): f/3

Coating Specification: R_{avg} >85% @ 400 - 700nm
R_{avg} >90% @ 400 - 2000nm

Effective Focal Length EFL (inches): 3.00

Focal Length Tolerance (%): ±2

Surface Accuracy: λ/4

Surface Quality:	60-40	Damage Threshold, Reference: ⓘ	0.3 J/cm ² @ 532nm & 1064nm, 10ns
Radius of Curvature (mm):	152.40	<div style="border: 1px solid black; padding: 5px; text-align: center;"> <p>Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.</p> <p>Select Your Country/Region:</p> </div>	
Regulatory Compliance			
RoHS 2015:	Compliant	Certificate of Conformance:	View
Reach 247:	Compliant		

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- Ideal for Multispectral Focusing Applications
- Variety of Coating Options Offered
- Multiple Sizes Available
- **λ/8 Precision Spherical Mirrors** Also Available

TECHSPEC® λ/4 Precision Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors are available in a wide range of metallic coating options covering the UV, VIS, and IR spectrum. A BOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® λ/4 Precision Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors collect and focus light without introducing chromatic aberration.

Technical Information


Related Products



Optical Cell Kinematic Mounts



Medium and Large Angle Mirror Mounts



Laser Mirror Substrates



λ/8 Precision Spherical Mirrors

Frequently Purchased Together




#32-711 - 20mm Dia. x 40mm FL
Uncoated, Double-Convex Lens
€35,75

Qty




€129,00

Qty



€35,75

Qty



#45-391 - 20mm, Aluminum &
MgF₂ Coated, N-BK7 Right
Angle Prism
€93,50

Qty

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Resources

Media Type

- Application Note
- Video
- FAQ
- Glossary

CASE STUDIES

Laser Optics
for Eye
Surgery

TRENDING IN OPTICS

Increasing
Challenges for
Sourcing Laser
Optics...

CASE STUDIES

Using IR
Spectroscopy
for Counterfeit
Drug Detection

APPLICATION NOTE

Metallic Mirror
Coatings

VIDEO

Optical Mirrors
Review

FAQ

What is the
difference
between a
first-surface...

[View More](#)