

TECHSPEC®

20.0mm Dia. x 40.0mm FL, NIR I Coated, Plano-Convex Lens



Stock **#48-759** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€41,50

ADD TO CART

Qty 1-9
€41,50
Qty 10+
€37,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):

40.00 @ 587.6nm
Back Focal Length BFL (mm): 36.77
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.90 ±0.10
Edge Thickness ET (mm): 2.32
Radius R₁ (mm): 20.67
Clear Aperture CA (mm): 19
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant