

TECHSPEC®

20.0mm Dia. x 80.0mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock **#47-890-INK** 3-5 DAYS
[Other Coating Options](#)

-

1

+

€51,50

ADD TO CART

Qty 1-9
€51,50
Qty 10+
€46,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 ±0.025

Effective Focal Length EFL (mm):

80.00 @ 587.6nm
Back Focal Length BFL (mm): 78.45
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.35 ±0.10
Edge Thickness ET (mm): 1.13
Radius R₁ (mm): 41.48
Clear Aperture CA (mm): 19
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View