

TECHSPEC® 1° Nom. VIS-NIR Coated, N-BK7 Wedge Prism



Stock **#45-558** 3-4 DAYS

- 1 + **€60,00**

ADD TO CART

Qty 1-5
€60,00

Qty 6+
€48,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS-NIR (400-1000nm)

Angle Tolerance (arcsec):
±30

Bevel:
Protective bevel as needed

Coating Specification: R_{abs} ≤0.25% @ 880nm R_{avg} ≤1.25% @ 400 - 870nm R_{avg} ≤1.25% @ 890 - 1000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 25.00 +0.00/-0.10
Image Orientation: Beam Deviation
Power (diopters): 1.74
Ray Deviation @ 633nm (°): 1.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 3.00
Type: Wedge Prism
Wavelength Range (nm): 400 - 1000
Wedge Angle: 1° 56'
Maximum Edge Thickness (mm): 3.8
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View