

[See all 10 Products in Family](#)

TECHSPEC® 1mm Diameter 45° Rod Mirror Aluminum Coated



45° Rod Mirrors

Stock #47-628 **8 In Stock**

⊖ 1 ⊕ €163.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€163,00 each
Qty 6-25	€147,00 each
Qty 26-49	€130,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Rod Lens **Type:**

Coating on Elliptical Surface **Note:**

Physical & Mechanical Properties

Diameter (mm):

1.00 +0.00/-0.05

Length (mm):

2.00

Bevel:

Protective as needed

Length Tolerance (mm):

±0.1

Optical Properties

Coating:

Protected Aluminum (400-700nm)

Substrate:

N-BK7

Surface Quality:

40-20

Angle Tolerance (arcmin):

±10

Coating Specification:

R_{avg} >85% @ 400 - 700nm

Ray Deviation (°):

90

Wavelength Range (nm):

400 - 700

Coating Type:

Metal

Damage Threshold, By Design:

0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015:

Compliant

Reach 219:

Compliant

Certificate of Conformance:

[View](#)

Product Details

- Protected Aluminum Coating
- Reflect Light at 90°

TECHSPEC® 45° Rod Mirrors are designed for use in a variety of laser and imaging systems. The mirrors can be used to redirect laser light at 90°. Their small diameters make them ideal for use in fiberscope/borescope applications where size is critical. TECHSPEC 45° Rod Mirrors feature polished elliptical surfaces and ground circumferences and bases. These components are available in a range of micro sizes for integration into a host of OEM applications.

Technical Information

