

[See all 33 Products in Family](#)

## 20 x 20mm, 800µm Pitch, 1.7° Div., Double Cyl. Lens Array UV-VIS



Stock #72-606 **3 In Stock**

- 1 + €765<sup>.00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€765,00 each
Qty 11+	€612,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Lens Array **Type:**

### Physical & Mechanical Properties

20.0 x 20.0 ±0.10 **Dimensions (mm):**

11.100 **Radius R (mm):**

2.00 ±0.10 **Thickness (mm):**

## Optical Properties

**Effective Focal Length EFL (mm):**  
24.70 @ 1064nm

**Substrate:**   
[Fused Silica](#) (Corning 7980)

**Coating:**  
UV-NIR (250-700nm)

**Wavelength Range (nm):**  
250 - 700

**Coating Specification:**  
R<sub>abs</sub> ≤1.0% from 350 - 450nm @ 0° AOI  
R<sub>avg</sub> ≤1.5% @ 250 - 700nm @ 0°

**Divergence Angle (°):**  
1.7 (Full Width)

**Pitch (µm):**  
800.00

**Array Type:**  
Double-Sided (with cross-oriented lenses)

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 250:**  
[Compliant](#)

## Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.