

[See all 56 Products in Family](#)

TECHSPEC® 20mm Dia., 2mm Thick, Uncoated, Gorilla Glass® Window



Gorilla® Glass Windows



Stock #29-722 [CONTACT US](#)

⊖ 1 ⊕ €34.⁵⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€34,50 each
Qty 6-25	€28,00 each
Qty 26-49	€26,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window **Type:**

8 **Chemical Strengthening Cycle (hours):**

Physical & Mechanical Properties

18.00 Clear Aperture CA (mm):

20.00 ±0.13 Diameter (mm):

2.00 ±0.10 Thickness (mm):

Protective as needed Bevel:

90.00 Clear Aperture (%):

Ground Edges:

0.22 Poisson's Ratio:

70 Young's Modulus (GPa):

Optical Properties

Uncoated Coating:

Gorilla® Glass Substrate:

1.5 Index of Refraction (n_d):

80-50 Surface Quality:

350 - 2200 Wavelength Range (nm):

Material Properties

2.39 Density (g/cm³):

7.58 (0 to +300°C) Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 247:


Product Details

- Chemically Strengthened Drawn Glass
- Highly Resistance to Surface Scratches
- Ideal for Electronic Displays

Gorilla® Glass Windows are chemically strengthened to reduce the propagation of surface flaws. These thin windows feature superior surface quality and excellent scratch resistance. With greater than 90% transmission from 350 - 600nm, these windows are excellent protective covers for electronic displays in consumer and industrial applications. Gorilla® Glass Windows are widely used as protective cover glass for high-end display devices such as laptops, televisions and mobile phones. Due to their durable construction, they are ideal for even the most demanding applications.

Technical Information

Gorilla® Glass 3
Typical Transmission



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Quote Your Size
