

[See all 18 Products in Family](#)

TECHSPEC® 20mm N-SF11 MgF₂ Coated Equilateral Prism



Equilateral Prisms

Stock #49-434 **15 In Stock**

⊖ 1 ⊕ €145⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | €145,00 each |
| Qty 6-25 | €116,00 each |
| Qty 26-49 | €108,75 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Equilateral Prism **Type:**

Physical & Mechanical Properties

20.00 **Length of Face (mm):**

Length (mm):

20.00

Dimensional Tolerance (mm):

±0.1

Optical Properties

Coating:

MgF₂ (400-700nm)

Substrate:

[N-SF11](#)

Surface Quality:

40-20

Angle Tolerance (arcmin):

±2

Image Orientation:

Dispersion

Coating Specification:

R_{avg} ≤ 1.75% @ 400 - 700nm

Wavelength Range (nm):

400 - 700

Power (fringes) @ 632.8nm:

2.50

Irregularity (fringes) @ 632.8nm:

0.50

Regulatory Compliance

Certificate of Conformance:


[View](#)

Product Details

- Ideal for Light Dispersion
- Sizes Ranging from 5 - 50mm
- Available Uncoated or Anti-Reflection Coated
- Additional [Equilateral Prism](#) Options Available

TECHSPEC® Equilateral Prisms feature three equal 60° angles and are often referred to as dispersing prisms. Equilateral prisms are ideal for wavelength separating applications and light dispersion. These prisms are available in sizes ranging from 5-50mm. Our TECHSPEC® Equilateral Prisms are offered uncoated or with a single layer MgF₂ anti-reflection coating. Additional [Equilateral Prism](#) options are available.

Technical Information



Coating Curves