

## 2.2 - 13.6um InAsSb Photovoltaic Infrared Detector, PVIA-4TE-13-1x1-TO8-wZnSeAR36



2.2 - 13.6um InAsSb Photovoltaic Infrared Detector, PMA-4TE-13-1x1-TO8-wZnSeAR36

Stock #90-464 **NEW** 4 In Stock

⊖ 1 ⊕ €2.525<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€2.525,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

IR Photovoltaic Detector **Type:**

PVIA-4TE-13-1x1-TO8-wZnSeAR36 **Model Number:**

TO-8 **Package:**

**Manufacturer:**

## Physical & Mechanical Properties

7 **Weight (g):**

1.00 x 1.00 **Active Area (mm):**

## Optical Properties

2200 - 13600 **Spectral Response (nm):**

36 **Acceptance Angle (°):**

## Environmental & Durability Factors

-40 to +70 **Operating Temperature (°C):**

-40 to +85 **Storage Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

## Product Details

- Mid and Long-Wave Infrared (MMR/LWIR) Spectral Range
- 1 × 1mm<sup>2</sup> Active Areas with Acceptance Angles up to 90°
- TO-39 and TO-8 Package Styles with Specialized Anti-Reflection Windows

Vigo Photonics Infrared Detectors deliver high-performance mid and long-wave IR detection with exceptional sensitivity and stability across demanding applications. These HgCdTe and InAsSb detectors are available with a variety of cooling configurations, including single, dual, triple, and quad-stage thermoelectric coolers, to optimize signal-to-noise ratios. Models are offered with active areas of 1 × 1mm<sup>2</sup> and acceptance angles up to 90°, providing flexibility for system integration. Vigo Photonics Infrared Detectors feature precision packaging options such as TO-39 and TO-8 housings with specialized anti-reflection coatings for maximum throughput. These detectors combine reliability with infrared technology, making them ideal for spectroscopy, gas analysis, and defense applications.