

## 22 x 48mm FL, Grade 2, Double-Convex Lens



Stock **#95-783** CLEARANCE **20+ In Stock**

-

1

+

€9<sup>.95</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €9,95 each                    |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

| Product Downloads |
|-------------------|
|-------------------|

### SPECIFICATIONS

#### Physical & Mechanical Properties

Diameter (mm):

22.00

#### Optical Properties

Effective Focal Length EFL (mm):

48.00

|                       |                             |
|-----------------------|-----------------------------|
| 2.18                  | f/#:                        |
| 0.23                  | Numerical Aperture NA:      |
| Regulatory Compliance |                             |
| <a href="#">View</a>  | Certificate of Conformance: |

## PRODUCT DETAILS

- Ideal for Experimenting and Prototyping Applications
  - Quantities Extremely Limited, Buy While Supplies Last
  - For Even More Deals, Check out [Mega Clearance: Optics](#)
- Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.
- 20 - 29.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.
- Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## TECHNICAL INFORMATION

