

[See all 23 Products in Family](#)

25 mm Travel, Motorized Linear Stage, Integrated Controller

See More by [Zaber™](#)



#15-285, 25 mm Travel, Motorized Linear Stage, Integrated Controller

Stock **#15-285** [CONTACT US](#)

-

1

+

€2.220⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.220,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Type:	
Metric	
Manual Control/ LED Indicators:	
Yes	
Manufacturer:	
Zaber Technologies Inc.	
Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232	

connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.	
2-Phase Stepper	Type of Motor:
Physical & Mechanical Properties	
Linear (X)	Type of Movement:
Needle Roller Bearing	Guide System:
45 x 162.6	Stage Size (mm):
25.4	Travel (mm):
15 (Unidirectional)	Accuracy (µm):
<12	Backlash (µm):
21	Height (mm):
10	Load Capacity (kg):
<25	Parallelism (µm):
<3	Repeatability (µm):
0.00003 to 26	Speed (mm/s):
0.33	Weight (kg):
75.80	Total Track (mm):
Optical Properties	
0.05	Resolution (µm):
Electrical	
350	Maximum Operating Current (mA):
Hardware & Interface Connectivity	
Precision Lead Screw	Type of Drive:
Power Supply Required and Sold Separately. USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294	Power Supply:
USB with #15-295 RS-232 with #15-297	Computer Interface:
Environmental & Durability Factors	
0 - 50	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- High Accuracy, 25mm, 50mm, 100mm, and 200mm Travel Options
- Integrated Motor and Controller
- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder
- Easily Configurable in X-Y or X-Y-Z Configurations
- Vacuum-Compatible Options

Zaber™ High Precision Motorized Stage Systems are computer-controlled, self-contained linear stages that include a stepper motor and built-in controller. Zaber™ High Precision Motorized Stage Systems can connect directly to a computer's RS-232 port, while the included software provides an easy method for controlling travel distance or position. Additionally, the manual control potentiometer permits smooth manual movement. Encoder versions are available for all travel lengths, with 200 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. The integrated rotary encoder provides closed-loop control and slip/stall detection and recovery.

Note: A bottom adapter plate (sold separately) is required for mounting to a standard metric or English breadboard. A 24-48 VDC universal power supply, data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories. Use Top Adapter Plate #68-644 to Mount 70mm TECHSPEC® Stages.

Technical Information

Device Overview / Connectors


Images are shown looking into the device.

Power


Pin	Description
1	24 - 48 V
2	GND (Note: power supplies ground this pin to AC Earth)

Note: To prevent damage to the device due to static buildup, the device should be properly grounded. The power supplies for X-Series devices are non-isolated and thus ground the device chassis to Earth via the negative terminal of the power supply. If for any reason you are using an isolated power supply, please ensure your device is grounded by connecting the negative terminal of the power connector to AC Earth.

#68-645



#68-644



#68-343

