


## 20mm Dia x 20mm Focal Length, Spherical Mirror



Stock #46-237 **1 In Stock**

- 1 + €53<sup>50</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-49	€53,50 each
Qty 50-99	€49,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Spherical Mirror **Type:**

#### Physical & Mechanical Properties

20.00 +0.00/-0.30 **Diameter (mm):**

Ground **Back Surface:**

Center Thickness CT (mm):

3.00

Center Thickness Tolerance (mm):

±0.30

Edge Thickness ET (mm):

4.27

Edges:

Ground

Radius R (mm):

40.0

## Optical Properties

Substrate:

N-BK7

Focal Length Tolerance (%):

±2

Surface Quality:

60-40

Surface Accuracy:

λ/4

Effective Focal Length EFL (mm):

20.00

Radius of Curvature (mm):

40.00

Aperture (f/#):

f/1

Coating:

Protected Aluminum (400-2000nm)

Coating Specification:

R<sub>avg</sub> >85% @400 - 700nm  
R<sub>avg</sub> >90% @400 - 2000nm

Coating Type:

Metal

Wavelength Range (nm):

400 - 2000

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

## Product Details

- Aluminum Coating
- Ideal for UV, Visible, and IR Applications
- Multiple Diameter and f/# Combinations Available

λ/4 Spherical Mirrors have flat rear surfaces and aluminum coated spherical front surfaces. These mirrors are ideal for applications in UV, VIS, and IR wavelength ranges.

## Technical Information

