

TECHSPEC® 20mm, Uncoated, High Tolerance N-BK7 Right Angle Prism



N-BK7 High Tolerance Right Angle Prisms

Stock **#32-547** **20+ In Stock**

⊖ 1 ⊕ €111.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€111,00 each
Qty 6-25	€88,50 each
Qty 26-49	€83,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Right Angle Prism **Type:**

Physical & Mechanical Properties

+0/-0.1 **Dimensional Tolerance (mm):**

Bevel:

Protective as needed

28.30 Length of Hypotenuse (mm):

20.00 Length of Legs (mm):

Optical Properties

±15 Angle Tolerance (arcsec):

Uncoated Coating:

N-BK7 Substrate:

40-20 Surface Quality:

Left-Handed Image Orientation:

90 Ray Deviation (°):

350 - 2200 Wavelength Range (nm):

1.25 Power (fringes) @ 632.8nm:

0.25 Irregularity (fringes) @ 632.8nm:

Regulatory Compliance

Compliant RoHS 2015:

Compliant Reach 219:



View Certificate of Conformance:

Product Details

- Ray Deviation of 90°
- Left Handed Image
- Low Arcsecond Angle Tolerance
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® High Tolerance N-BK7 Right Angle Prisms are generally used to bend image paths or redirect light at 90°. This process produces a left-handed image, depending on the prism's orientation, the image may be inverted or reverted. Right angle prisms can also be combined for image/beam displacement. TECHSPEC® High Tolerance N-BK7 Right Angle Prisms feature low arcsecond angle tolerance and are made from precision N-BK7 for use in a variety of visible light applications. These prisms are available uncoated, with a protective aluminum overcoat, or MS[®] & aluminized.

Technical Information





Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram