

TECHSPEC[®] 2.0X In-Line Illumination SilverTL[™] Telecentric Lens



2.0X In-Line Illumination SilverTL[™] Telecentric Lens, #88-348



Stock **#88-348** 20+ In Stock

-

1

+

€2.145⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.145,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

SilverTL[™] Series

Product Family:

Stock No. of Mounting Clamp:
#56-870 Sold Separately

Type:

Telecentric Lens

In-Line Illumination		Type of Illumination:
Physical & Mechanical Properties		
Variable	Iris Option:	
144.60	Length (mm):	
144.60	Length excluding Threads (mm):	
45.00	Maximum Diameter (mm):	
314	Weight (g):	
Anodized Aluminum	Construction:	
Optical Properties		
4.4mm	Horizontal Field of View, 2/3" Sensor:	
3.2mm	Horizontal Field of View, 1/2" Sensor:	
2.4mm	Horizontal Field of View, 1/3" Sensor:	
11.00	Maximum Image Circle (mm):	
0.164	Numerical Aperture NA, Object Side:	
±3	Working Distance Tolerance (mm):	
>40% @ 40 lp/mm	Resolution, Image Space MTF @ f/10:	
8 (7)	Number of Elements (Groups):	
<0.075	Typical Telecentricity @ 588nm (°):	
<0.040	Typical Distortion @ 588nm (%):	
2X	Primary Magnification PMAG:	
2.00	Telecentric Lens Magnification:	
75.00	Working Distance (mm):	
4.4 x 3.3	FOV @ Max Sensor Format, H x V (mm):	
f/10 - f/22	Aperture (f/#):	
425 - 675nm BBAR	Coating:	
±0.13 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):	
2X	Magnification:	
VIS	Lens Wavelength Range:	
Sensor		
2/3"	Maximum Sensor Format:	
2.74	Pixel Size (µm):	
Threading & Mounting		
M43 x 0.75 (Female)	Filter Thread:	
C-Mount	Mount:	
Regulatory Compliance		
Compliant	RoHS 2015:	
Compliant	Reach 224:	


Product Details

- High Resolution f/6 Bi-Telecentric Lens with Inline Illumination Options
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Up to 2/3", C-Mbunt Telecentric Lens
- Magnification from 0.16X to 4X


TECHSPEC® SilverTL™ Telecentric Lenses are ideal for both on-line and off-line machine vision production applications that require accurate measurements. These lenses combine high-quality optics with a simplified non-focusing mechanical design and an adjustable iris with a locking set screw. These lenses are designed for metrology and gauging applications. TECHSPEC® SilverTL™ Telecentric Lenses also offer inline illumination options for maximum versatility. Each lens also features a standard front filter thread for use with [color filters](#), [polarizers](#), [protective windows](#), and [illumination adapters](#) for LED or fiber-optic ring lights.

Note: Mounting brackets are available that fit the 30mm diameter mounting surface.


Technical Information




#88-348, 2.0X In-Line Illumination SilverTL™ Telecentric Lens, Distortion Plot




#88-348, 2.0X In-Line Illumination SilverTL™ Telecentric Lens, Relative Illumination Plot




#88-348, 2.0X In-Line Illumination SilverTL™ Telecentric Lens, Telecentricity Plot



#88-348, 2.0X In-Line Illumination SilverTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 75mm Working Distance, f10



#88-348, 2.0X In-Line Illumination SilverTL™ Telecentric Lens, Depth of Field Plot, 75mm Working Distance, f10



#88-348, 2.0X In-Line Illumination SilverTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 75mm Working Distance, f10



#88-348, 2.0X In-Line Illumination SilverTL™ Telecentric Lens, Depth of Field Plot, 75mm Working Distance, f16

Stock Number	Primary Mag.	Max. Diameter A	Mounting Diameter B	Length C	Mounting Length D	Mounting Offset E	Filter Thread F
#56-675	0.16X	65mm	30mm	191mm	50mm	43mm	M62 x0.75
#63-073	0.20X	60mm	30mm	188mm	42mm	45mm	M58 x0.75
#56-676	0.25X	48mm	30mm	158mm	49mm	44mm	M46 x0.75
#58-428	0.30X	46mm	30mm	158mm	60mm	43mm	M43 x0.75
#56-677	0.40X	45mm	30mm	159mm	67mm	33mm	M43 x0.75
#63-074	0.50X	40mm	30mm	153mm	42mm	68mm	M37 x0.75
#88-344 (In-Line)	0.60X	42mm	30mm	156.2mm	45.1mm	73.4mm	M40.5 x0.5
#56-678				156mm	57mm	46mm	
#67-731				151.2mm	34mm*	82.2mm	
#88-346 (In-Line)	0.75X	36mm	30mm	155.2mm	46.2mm	16.9mm	M30.5 x0.5
#58-430				114mm	32mm*	17mm	
#58-431	2.0X	45mm	30mm	141mm	45mm	17mm	M43 x0.75
#88-348 (In-Line)	4.0X	61mm	30mm	144.6mm	42.2mm	18.8mm	M58 x0.75
#58-432				249mm	99mm	17mm	



*Mounting clamp fits over iris

