

## 2.15" 625nm, LED Darkfield Illuminator

See More by [Advanced Illumination](#)



Stock #66-791 3-4 DAYS

⊖ 1 ⊕ **€395,00**

**ADD TO CART**

Qty 1+

€395,00

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Color:**  
Red

**Height (mm):**  
19.0

**Inner Diameter (mm):**  
19.0

**Model Number:**  
RL2115-660-24

**Mount:**  
Standard

**Operating Temperature (°C):**  
0 to +65

**Outer Diameter (mm):**  
55.0

**Mounting Threads:**  
M3 x2

**Wavelength (nm):**  
625.00

**Working Distance (mm):**  
19 - 25.4

**LED Lifetime (hours):**  
50,000

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#66-855](#)  
Europe: [#66-855](#)  
Japan: [#66-855](#)  
Korea: [#33-773](#)  
China: [#66-855](#)

**Number of LEDs:**  
15.00

**Number of Channels:**  
1.00

**Field Coverage (mm):**  
6.4 - 12.7

**Maximum Trigger Frequency (Hz):**  
30.00

**Type of Illumination:**  
LED Illuminator

**Note:**  
Requires a 24V power supply [#66-855](#). European power supply [#35-200](#) also available.

**Manufacturer:**  
Advanced Illumination

**Geometry:**  
Ring Light

**Illumination Mode:**  
Constant

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 233:**  
[Compliant](#)

---