

[See all 53 Products in Family](#)

2.1mm FL, IR-Cut Filter at 650nm, f/2, Micro Video Lens



Stock **#66-883** 20+ In Stock

-

1

+

€70^{.00}

ADD TO CART

Volume Pricing	
Qty 1-49	€70,00 each
Qty 50+	€56,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Product Family:	Long Working Distance Optimized Imaging Lenses
Note:	IR Cut-Off Filter Included
Type:	M12 Imaging Lens
IR Cut Filter:	Yes

Special Type of Lens:	
IR-Cut Filter	
Physical & Mechanical Properties	
Iris Option:	
Fixed	
Length (mm):	
18.30	
Maximum Diameter (mm):	
17.0	
Outer Diameter (mm):	
17	
Optical Properties	
Horizontal Field of View @ Max Sensor Format:	
131	
Maximum Image Circle (mm):	
6.00	
Resolution, On-Axis:	
100 lp/mm @ 20% Contrast	
Resolution, 0.7 Field:	
63 lp/mm @ 20% Contrast	
Resolution, Full Field:	
40 lp/mm @ 20% Contrast	
Focal Length FL (mm):	
2.10	
Working Distance (mm):	
400 - ∞	
Aperture (f/#):	
f/2	
Distortion (%):	
-82.4 @ Full Field	
Maximum Distortion (%):	
-82.4	
Lens Wavelength Range:	
VIS (IR-Cut Filter)	
Sensor	
Maximum Sensor Format:	
1/3"	
Pixel Size (µm):	
3.45	
Threading & Mounting	
Filter Thread:	
M12 x 0.50	
Mount:	
S-Mbunt (M12 x 0.5)	
Regulatory Compliance	
RoHS 2015:	
Exempt	
Certificate of Conformance:	
View	
Reach 242:	
Contains SVHC(s)	

Product Details

- Up to 2/3", S-Mbunt Lens
- Wide Field of View Board Camera Lens
- 1.68mm to 50mm Focal Length

Long Working Distance Optimized Imaging Lenses are designed for use in micro sensor board cameras. These lenses provide excellent image quality in a small, versatile package. Optimized to cover 2/3" sensor formats, they are an ideal choice for wide angle and close focus applications. Long Working Distance Optimized Imaging Lenses have 1.68 to 50mm focal lengths. All lenses are threaded for M12 x 0.5. Some models with Back Focal Distances (dimension "C") less than 4mm may be incompatible with some color cameras due to the camera's Bayer filter. We recommend such lenses for use with monochrome cameras only. Lenses are designed for the 400nm to 700nm range.

Note: A line of [M12 Imaging Lens Accessories](#) is available for these products.

Technical Information



Infinite Conjugate M12 Imaging Lenses



C-Mount Adapter (#53-675)

Stock #		Focal Length (mm)	Aperture (f/#)	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)
No-IR Cut Filter	IR Cut Filter @650nm							
#59-776	#66-880	1.68	2.5	15.0	13.2	3.3	2.8	15.1
#56-774	#66-881**	1.74	2.8	21.0	19.61	3.33	3.2	N/A
#64-106	-	1.9	2.0	17.0	14.58	4.2	4.0	15.24
#55-569	#66-883	2.1	2.0	17.0	18.3	4.8	3.7	19.4
#57-681	#66-884***	2.5	2.5	17.0	19.1	4.4	3.7	20.3
#55-570	#66-885	2.9	2.0	15.0	17.4	5.2	5.8	17.8
#59-778	#66-886	3.0	2.0	14.0	15.3	5.3	3.9	N/A
#57-684	#66-890	6.05	1.8	15.0	15.6	8.0	6.0	N/A
#55-573	#66-891	6.37	2.4	14.8	13.12	5.3	3.3	N/A
#55-574	#66-892	8.0	2.5	15.0	13.5	5.8	3.0	N/A
#63-762	#59-779	10.1	2.8	15.0	13.4	6.1	3.2	N/A
#65-251	#64-107	10.4	2.8	14.0	8.93	6.4	4.0	N/A
#56-775	#66-893	12.0	2.0	14.0	12.1	6.2	4.0	N/A
#64-108	#66-894	16.0	2.0	14.0	14.4	8.0	4.5	N/A
#83-107	-	16.0	4.0	14.0	14.4	8.0	4.5	N/A
#56-776	#66-895	25.0	2.5	25.0	23.2	8.1	6.7	N/A
#59-780	#66-896	35.0	2.0	25.0	23.4	15.8*	6.0	N/A
#59-781	#66-897	50.0	2.5	27.0	52.8	4.1	8.0	N/A
*Note: 35.0mm lens has a large flange focal length. Please make proper adjustments when mounting. **#66-881, B(mm): 20.49 ***#66-884, B(mm): 19.8, E(mm): 21								

Stock #	Focal Length (mm)	Aperture (f/#)	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)
#88-587	3.0	2.0	15.0	15.35	5.2	4	16
#88-588	3.5	2.5	15.0	15.4	6.9	4	N/A
#11-323	3.7	1.6	19	24.04	5.46	6.5	24.16
#11-324	4.0	1.8	20	23.8	5.01	7	24.72
#88-589	4.0	2.0	15.0	16.1	5.9	3.8	N/A
#88-590	4.3	2.0	22.0	20.96	5.5	6	21.93
#11-325	4.6	1.6	19	24.18	5.44	7	24.32
#88-591	4.6	2.0	12.0	13.1	1.9	6	N/A
#88-592	5.6	2.0	17.0	22.21	5.3	5	22.38
#89-750	6.0	2.0	14.0	15.1	6.7	3.93	N/A
#11-326	7.0	1.6	19	25.24	5.47	7.2	24.2
#89-751	8.0	2.0	15.0	14.4	6.8	4.5	N/A
#89-752	12.0	2.0	15.0	14.3	5.7	4.5	N/A

