

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Dia. 532nm U-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock #38-893 3-4 DAYS



1



€166,00

ADD TO CART

Qty 1-5

€166,00

Qty 6+

€147,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:  
10-5

Type:  
Laser Mirror

Parallelism (arcmin):  
<3

|                                                                                              |
|----------------------------------------------------------------------------------------------|
| <b>Clear Aperture (%)</b> :<br>90                                                            |
| <b>Back Surface:</b><br>Commercial Polish                                                    |
| <b>Reflection at DWL (%)</b> :<br>99.8                                                       |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≥99.8% @ 532nm                             |
| <b>Wavelength Range (nm)</b> :<br>523 - 537                                                  |
| <b>Surface Flatness (P-V):</b><br>λ/10                                                       |
| <b>Coating Type:</b><br>Dielectric                                                           |
| <b>Coating:</b><br>Laser Mirror (532nm)                                                      |
| <b>Design Wavelength DWL (nm)</b> :<br>532                                                   |
| <b>Diameter (mm)</b> :<br>25.40 +0.00/-0.10                                                  |
| <b>Thickness (mm)</b> :<br>6.35 ±0.2                                                         |
| <b>Angle of Incidence (°)</b> :<br>0-45                                                      |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)    |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>10 J/cm² @ 532nm, 20ns, 20Hz |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |