

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4 X 25.4mm X -50mm FL, Uncoated Laser Grade PCV Cylinder Lens



TECHSPEC Beam Shaping Fused Silica Cylinder Lenses

Stock #36-095 In Stock



1



€143,00

ADD TO CART

Qty 1-5

€143,00

Qty 6+

€114,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-50.00

Substrate:
[Fused Silica](#) (Corning 7980)

f/#:
2.00

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 200 - 2200
Back Focal Length BFL (mm): -52.06
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 6.64
Radius R₁ (mm): 22.93
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <3
Power Axis Wedge (arcmin): <4.5
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View