

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Dia. X 25.4mm EFL, 532nm Dielectric Off-Axis Parabolic Mirror



TECHSPEC® Laser Line Coated Off-Axis Parabolic (OAP) Mirrors

Stock #15-345 3-4 DAYS

[Other Coating Options](#)



1



€313,00

ADD TO CART

Qty 1-5

€313,00

Qty 6+

€281,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.0/-0.1

Effective Focal Length EFL (mm):

25.40
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 25.40
Coating: Dielectric Mirror (532nm)
Coating Type: Dielectric
Coating Specification: R _{avg} >99.5% @ 532nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 12.7
Surface Figure, RMS: λ/8
Surface Roughness (Angstroms): <50 RMS
Wavelength Range (nm): 532
Clear Aperture (%): 90
Surface Quality: 60-40
Compatible Mounting Plates: #47-111
Substrate: Aluminum 6061-T6
Y Offset (mm): 25.4
Reflected Wavefront, RMS: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant