


25.4mm Dia. 488nm 0°, Low Cost Laser Line Mirror



Stock #11-079 3-4 DAYS

⊖ 1 ⊕ **€118,00**

ADD TO CART

Qty 1-10
€118,00
Qty 11+
€105,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
20-10

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%): 90
Durability: ML-C-675C
Back Surface: Commercial Polish
Reflection at DWL (%): 99
Coating Specification: Rabs >99% @488nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (488nm)
Design Wavelength DWL (nm): 488
Diameter (mm): 25.40 +0.0/-0.1
Thickness (mm): 6.35 ±0.2
Angle of Incidence (°): 0
Substrate: N-BK7

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View