

[See all 4 Products in Family](#)

# 25.4mm Dia., 4mm Thick, 30' Wedge, ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Window | BF-WW-25-4

See More by [ISP Optics](#)



Barium Fluoride (BaF<sub>2</sub>) Wedged Windows



Stock #16-806 **CLEARANCE** 6 In Stock

- 1 + €389<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€389,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Model Number:  
BF-WW-25-4

Type:  
Protective Window

Crystal **Type of Window:**

## Physical & Mechanical Properties

21.59 **Clear Aperture CA (mm):**

25.40 +0.00/-0.13 **Diameter (mm):**

4.00 ±0.13 **Thickness (mm):**

Protective as needed **Bevel:**

85 **Clear Aperture (%):**

Fine Ground **Edges:**

0.34 **Poisson's Ratio:**

53 **Young's Modulus (GPa):**

82.00 **Knoop Hardness (kg/mm<sup>2</sup>):**

30±15 arcmin **Wedge Angle (arcmin):**

## Optical Properties

Uncoated **Coating:**

[Barium Fluoride \(BaF<sub>2</sub>\)](#) **Substrate:**

1.478 @ 0.5µm  
1.451 @ 5µm  
1.401 @ 10µm **Index of Refraction (n<sub>d</sub>):**

60-40 **Surface Quality:**

81.78 **Abbe Number (v<sub>d</sub>):**

200 - 12000 **Wavelength Range (nm):**

2λ @ 633nm **Surface Flatness (P-V):**

## Material Properties

4.89 **Density (g/cm<sup>3</sup>):**

18.1 **Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

## Product Details

- 30 Arcmin Wedge
- Excellent Transmission from 200nm - 12µm
- Resistant to High-Energy Radiation
- [Precision Flat Barium Fluoride \(BaF<sub>2</sub>\) Windows](#) Also Available

ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Windows feature a 30 arcmin wedge to eliminate etalon effects, improving readout in detection and spectroscopy applications. With a low index of refraction of 1.48, these windows provide high transmission from 200nm to 12µm without the need of an anti-reflection (AR) coating. Barium fluoride windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the vacuum ultraviolet range. ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Windows are ideal for infrared spectroscopy, thermal imaging, and general UV-IR detection applications. Barium fluoride is also a fast scintillator and can be used for the detection X-rays, gamma rays, or other high energy particles.

**Note:** These optical windows are very sensitive to thermal shock.

## Technical Information

