

TECHSPEC®

25.0mm Diameter x 25.0mm FL, 980nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses

Stock **#69-562** CLEARANCE 3-4 DAYS

[Other Coating Options](#)



1



€20,95

ADD TO CART

Qty 1+

€20,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Back Focal Length BFL (mm):
20.22

Coating:

Laser V-Coat (980nm)
Coating Specification: R _{abs} <0.25% @ 980nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 8.00 ±0.10
Edge Thickness ET (mm): 2.43
Radius R₁ (mm): 16.82
Clear Aperture CA (mm): 24
f/#: 1.00
Numerical Aperture NA: 0.50
Design Wavelength DWL (nm): 980
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm ² @ 980nm, 10ns

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View