

[See all 30 Products in Family](#)

25.4mm Dia., 515nm, $\lambda/4$ High Energy Waveplate



High Energy Quartz Waveplates

Stock **#39-168** **1 In Stock**

-

1

+

€655⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€655,00 each
Qty 11+	€610,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
High Energy Waveplate	Type:
Physical & Mechanical Properties	
18.0	Clear Aperture CA (mm):
25.40	Diameter (mm):

+0/-0.2		Dimensional Tolerance (mm):
Optically Bonded on UVFS (C7980) Substrate		Construction:
<3		Parallelism (arcsec):
Optical Properties		
R _{avg} <0.2%		Coating:
515		Design Wavelength DWL (nm):
Crystalline Quartz		Substrate: ☐
λ/4		Retardance:
20-10		Surface Quality:
<λ/10 @ 632.8nm		Transmitted Wavefront, P-V:
λ/250 @ 20°C		Retardance Tolerance:
>20 J/cm² @ 1064nm, 10ns, 10Hz		Damage Threshold, By Design: ☐
1st		Retardance Order:

Threading & Mounting	
6 ±0.2	Mount Thickness (mm):

Regulatory Compliance	
Compliant View	RoHS 2015: Certificate of Conformance:
	Reach 247:

Product Details

- Damage Threshold up to >20 J/cm² @ 1064nm
 - λ/4 and λ/2 Retardance
 - Black Anodized Aluminum Mount
 - UV to NIR Design Wavelengths Available
- High Energy Quartz Waveplates are available in both λ/4 and λ/2 retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm² at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.