

**TECHSPEC® 25.4mm Dia., 532 & 1064nm T, 266nm R 45° Harmonic Separator**



TECHSPEC Nd:YAG Harmonic Separators

Stock #11-546 **20+ In Stock**

⊖ 1 ⊕ €381<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€381,00 each
Qty 6-24	€343,00 each
Qty 25-49	€305,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Harmonic Beamsplitter **Type:**

**Physical & Mechanical Properties**

>90 **Clear Aperture (%):**

**Construction:**

Dichroic	
25.40 +0.00/-0.10	<b>Diameter (mm):</b>
<3	<b>Parallelism (arcmin):</b>
6.35 ±0.20	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
45	<b>Angle of Incidence (°):</b>
<b>Coating Specification:</b>	
Surface 1: R <sub>abs</sub> : >95% @ 266nm, T <sub>abs</sub> : >98% @ 532nm, T <sub>abs</sub> : >98% @ 1064nm	
Surface 2: R <sub>abs</sub> : <1.0% @ 532nm, R <sub>abs</sub> : <1.0% @ 1064nm	
266	<b>Reflection Wavelength (nm):</b>
<a href="#">Fused Silica</a> (Coming 7980)	<b>Substrate:</b> <input type="checkbox"/>
M10	<b>Surface Flatness (P-V):</b>
10-5	<b>Surface Quality:</b>
532, 1064	<b>Transmission Wavelength (nm):</b>
<b>Damage Threshold, By Design:</b> <input type="checkbox"/>	
Surface 1:	
1 J/cm <sup>2</sup> @ 266nm, 20ns, 20Hz	
5 J/cm <sup>2</sup> @ 532nm, 20ns, 20Hz	
7.5 J/cm <sup>2</sup> @ 1064nm, 20ns, 20Hz	
Surface 2:	
10 J/cm <sup>2</sup> @ 20ns, 20Hz @ 532nm	
15 J/cm <sup>2</sup> @ 20ns, 20Hz @ 1064nm	
<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

**Note:** The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

## Compatible Mounts

;