

25.4mm Dia. f/0.75 NIR Coated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#33-266** 3-4 DAYS

⊖ 1 ⊕

€70,00

ADD TO CART

Qty 1-10
€70,00

Qty 11+
€58,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40 ±0.1

Effective Focal Length EFL (mm):
19.10 @ 632.8nm

Numerical Aperture NA: 0.67
Back Focal Length BFL (mm): 12.7
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: BBAR (700-1100nm)
Coating Specification: R _{avg} <0.5% @ 700 - 1100nm
Clear Aperture CA (mm): 23.9
Edge Thickness ET (mm): 4
Center Thickness CT (mm): 12.22
f/#: 0.75
Bevel: Protective bevel as needed
Operating Temperature (°C): 80
Radius R (mm): 49.78
Type: Aspheric Lens
Wavelength Range (nm): 700 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
