

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Dia. X 50.8mm EFL, 532nm Dielectric Off-Axis Parabolic Mirror



TECHSPEC® Laser Line Coated Off-Axis Parabolic (OAP) Mirrors

Stock #15-346 3-4 DAYS

[Other Coating Options](#)



1



€313,00

ADD TO CART

Qty 1-5
€313,00

Qty 6+
€281,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.0/-0.1

Effective Focal Length EFL (mm):

50.80
Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 50.80
Coating : Dielectric Mirror (532nm)
Coating Type : Dielectric
Coating Specification : R _{avg} >99.5% @ 532nm
Off-Set Angle (°) : 90
Parent Focal Length PFL (mm) : 25.4
Surface Figure, RMS : λ/8
Surface Roughness (Angstroms) : <50 RMS
Wavelength Range (nm) : 532
Clear Aperture (%) : 90
Surface Quality : 60-40
Compatible Mounting Plates : #47-111
Substrate : Aluminum 6061-T6
Y Offset (mm) : 50.8
Reflected Wavefront, RMS : λ/4

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 233 : Compliant