

**TECHSPEC® 25.4mm Dia., 6.35mm Thick, 532nm, λ/10 N-BK7 Window**



TECHSPEC λ/10 Laser Line Coated Windows

Stock **#38-963** CLEARANCE 3-4 DAYS

⊖ 1 ⊕ **€99,95**

ADD TO CART

Qty 1+

€99,95

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Angle of Incidence (°):**  
0

**Clear Aperture CA (mm):**  
22.86

**Coating:**  
Laser V-Coat (532nm)

**Design Wavelength DWL (nm):**  
532

|                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------|
| <div>Diameter (mm):<br/>25.40 +0.00/-0.10</div>                                                                  |
| <div>Substrate: <div><div></div><div>N-BK7</div></div></div>                                                     |
| <div>Index of Refraction n<sub>d</sub>:<br/>1.516</div>                                                          |
| <div>Surface Quality:<br/>10-5</div>                                                                             |
| <div>Thickness (mm):<br/>6.35 ±0.20</div>                                                                        |
| <div>Type:<br/>Laser Line Window</div>                                                                           |
| <div>Parallelism (arcmin):<br/>&lt;3</div>                                                                       |
| <div>Bevel:<br/>Protective as needed</div>                                                                       |
| <div>Clear Aperture (%):<br/>90</div>                                                                            |
| <div>Abbe Number (v<sub>d</sub>):<br/>64.17</div>                                                                |
| <div>Coating Specification:<br/>R<sub>abs</sub> &lt;0.25% @ 532nm</div>                                          |
| <div>Surface Flatness (P-V):<br/>λ/10</div>                                                                      |
| <div>Damage Threshold, By Design: <div><div></div><div>10 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz</div></div></div> |
| <div>Edges:<br/>Fine Ground</div>                                                                                |

## Regulatory Compliance

|                                                 |
|-------------------------------------------------|
| <div>RoHS:<br/>Compliant</div>                  |
| <div>Certificate of Conformance:<br/>View</div> |