

[See all 133 Products in Family](#)

**TECHSPEC® 25.4mm Diameter x 2000mm FL, 1900-2200nm Coated, IR Ultrafast Thin PCX Lens**



Stock #11-632 **17 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €208<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €208,00 each                  |
| Qty 6-25       | €182,00 each                  |
| Qty 26-49      | €166,40 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

25.40 +0.00/-0.10 **Diameter (mm):**

|   |   |
|---|---|
| <3                                      | <b>Centering (arcmin):</b>              |
| 1.60 ±0.10                              | <b>Center Thickness CT (mm):</b>        |
| 1.512                                   | <b>Edge Thickness ET (mm):</b>          |
| 22.86                                   | <b>Clear Aperture CA (mm):</b>          |
| Protective as needed                    | <b>Bevel:</b>                           |
| <b>Optical Properties</b>               |   |
| 2,002.33 @ 587.6nm                      | <b>Effective Focal Length EFL (mm):</b> |
| 2001.23                                 | <b>Back Focal Length BFL (mm):</b>      |
| BBAR (1900-2200nm)                      | <b>Coating:</b>                         |
| R <sub>abs</sub> <0.15% @ 1900 - 2200nm | <b>Coating Specification:</b>           |
| Fused Silica IR Grade                   | <b>Substrate:</b> □                     |
| 20-10                                   | <b>Surface Quality:</b>                 |
| 1.5λ                                    | <b>Power (P-V) @ 632.8nm:</b>           |
| λ/8                                     | <b>Irregularity (P-V) @ 632.8nm:</b>    |
| ±1                                      | <b>Focal Length Tolerance (%):</b>      |
| 918.00                                  | <b>Radius R<sub>1</sub> (mm):</b>       |
| 78.75                                   | <b>f#:</b>                              |
| 0.01                                    | <b>Numerical Aperture NA:</b>           |
| 1900 - 2200                             | <b>Wavelength Range (nm):</b>           |
| 0                                       | <b>Angle of Incidence (°):</b>          |

## Regulatory Compliance

|                      |                                    |
|----------------------|------------------------------------|
| <a href="#">View</a> | <b>Certificate of Conformance:</b> |
|----------------------|------------------------------------|

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ultra-Thin Center Thickness to Limit GDD
- Low Loss Broadband IBS Anti-Reflection Coating
- Ideal for Ultrafast and Laser Optics Applications
- UV or IR Grade Fused Silica Substrates

TECHSPEC® Ultrafast Thin Plano-Convex Lenses are designed with an ultra-thin center thickness to provide a low group delay dispersion (GDD) for ultrafast laser pulses. TECHSPEC Ultrafast Thin Plano-Convex Lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics, including Ti:sapphire, Yb:YAG, and Nd:YAG, Holmium, and Thulium lasers. These thin PCX lenses are available in standard sizes with effective focal lengths from 50mm to 2000mm.

IR grade fused silica differs from UV grade fused silica by its reduced amount of OH<sup>-</sup> ions, resulting in higher transmission throughout the NIR spectrum and reduction of transmission in the UV spectrum.

## Technical Information

Calculated GVD of Fused Silica



## Compatible Mounts

---