


TECHSPEC® 25.4mm Diameter x 250mm FL, 370-550nm Coated, Ultrafast Thin PCX Lens



Stock **#11-680** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€132,00**

ADD TO CART

Qty 1-5
€132,00

Qty 6+
€116,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
250.29 @587.6nm

Back Focal Length BFL (mm):

249.19
Coating: BBAR (370-550nm)
Coating Specification: R _{abs} <0.55% @ 370 - 550nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 0.9
Radius R₁ (mm): 114.75
Clear Aperture CA (mm): 22.86
f/#: 9.85
Numerical Aperture NA: 0.051
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 370 - 550
Angle of Incidence (°): 0
Damage Threshold, By Design: ☐ 7.5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View